

The greatest selection of matrix systems Rubber dam clamps **Polishing & Finishing**

Sectional Contoured Metal Matrices

- Anatomically pre-shaped
- Six typesProvide tight anatomical contact
- Stainless steel, 0.050 mm thick, hard / soft 0.035 mm thick, hard / soft

Available Packages:

#1.398 Kit of Sectional Matrices Matrices of 6 types, 100 pcs+2 rings



#1.298 Kit of Sectional Matrices Matrices of 5 types, 50 pcs + ring

#1.198 Kit of Sectional Matrices Matrices of 4 types, 30 pcs + ring

Refills: #1.0971-1.0976 #1.0971(50)-1.0976(50)

Clinical Cases & Operating Positions





Lug Metal Matrices

- Anatomically pre-shaped Adjastable contact point Stainless steel, 0.050 mm thick 0.035 mm thick

- 0.035 mm thick Lugs to pull matrix to adjacent tooth

Available Packages:

#1.368 Kit of Lug Matrices Matrices of 7 types 30 pcs., MD ring 1 pc. #1.338 / #1.348 Kit of Lug Matrices Matrices of 3 types 18 pcs., MD ring 1 pc.





New







Clinical Cases & Operating Positions





Saddle Metal Matrices

- Easy-to-use matrix system
 Optimal approximal contact without difficulties
 Three lengths for all posteriors
- Stainless steel, 0.035 mm & 0.050 mm thick

Edges of matrix are performed as cylinder-shape tubes where tines of ring or springclip are inserted upon matrix installation.



#1.310 / #1.320 Matrices of 3 types with springclip / ring 18 pcs.



#1.330 #1.330 Universal kit with springclip. Matrices of 3 types, 3 shapes, flat & contoured 36 pcs.

Refills: #1.311-1.313 Contoured matrices. 12 pcs. #1.301-1.303 Flat matrices. 12 pcs.

Clinical Cases & Operating Positions





Black Sectional Contoured Metal Matrices New



Rings

Forceps

High-quality stainless steel,Good shape memoryRound and flat tines

#1.0976B Black Sectional Contoured Metal Matrices, Medium, 50 pcs.



Extra loop on the ring makes it more flexible and allows to operate in wider range of openings without increase of residual distance between

Double tines of Delta ring are suitable for installation of fixing wedges & add-on wedges

Double tines of MD-rings with sides curved inwards and out are suitable for installation on both mesial and distal sides of the tooth over fixing wedges

#1.099-2 Forceps #1.099-2 have special stoppers, that allows to use them also for installation of Elastic wedges # 1.808

Forceps ##1.099-1, 1.099-2, 1.099-3 are applied for installation of rings for all TOR VM matrix systems

#1.099-3

tines after use

Sectional contoured metal matrices of black series (black matrices) provide anti-reflection effect for more convenient work.

Fixing Accessories for Sectional Matrices

#1.099(5) / #1.099(4) / #1.099(6) Standard / Low / High Ring, tines height 5 / 4 / 6 mm

#1 099A

#1.199 (flat tines)

#1.299 (Delta ring)

#1.167 (MD-ring)

#1.099c Ring with Safety Cover

Matrix Pliers



#1 154 #1.154 Linear Plier (L-Plier) 1 pc.

#1 164 Cross Plier (C-Plier) 1 pc.



New

L-Plier

Proxicut Systems

Intended use:

- to remove excess of filling material
- from interproximal areas, for tooth separation upon veneer fixation
- Consists of:
- proxicut saw blades proxicut diamond strips of 3 types,
- proxicut holders of 2 types

Available packages:



#1.370
Do-All Proxicut System saw blades - 12 pcs., strips - 3 types per 12 pcs. holder with key 1 pc., handle 1 pc.

#1.389 Proxicut Holder 1 pc.

Refills:

#1.384 Proxicut Saw Blades, 0,05 mm thick, 12 pcs

#1.385K / #1.385C / #1.385M Proxicut Diamond Strips coarse / medium / fine, 12 pcs.

#1.369 Do-All Proxicut Holder (holder with key 1 pc.)

#1.367KT / #1.369KT Do-All Proxicut Kit (holder with key 1 pc., handle #1.107 / #1.109 1 pc.)

Operating Positions





Strip Holders



Double slot system allows to fixate both metal and plastic strips with abrasive and/or smooth surfaces



#1.105 Anterior Strip Holder, 1 pc.



Operating positions





Shapes of Saddle Matrices

Refills of 3 shapes are available				
	Small Matrices 12 pcs. per box	Medium Matrices 12 pcs. per box	Large Matrices 12 pcs. per box	
Standard shape	Nº 1.301(1)	Nº 1.302(1)	Nº 1.303(1)	
Shape with flexible central part	Nº 1.301(2)	Nº 1.302(2)	Nº 1.303(2)	
Shape with enlarged undergingiva ledge	Nº 1.301(3)	Nº 1.302(3)	Nº 1.303(3)	

Shapes of Saddle Contoured Matrices Refills of 3 shapes are available				
	Small Matrices 12 pcs. per box	Medium Matrices 12 pcs. per box	Large Matrices 12 pcs. per box	
Standard shape	Nº 1.311(1)	Nº 1.312(1)	Nº 1.313(1)	
Shape with flexible central part	Nº 1.311(2)	Nº 1.312(2)	Nº 1.313(2)	
Shape with enlarged undergingiva ledge	Nº 1.311(3)	Nº 1.312(3)	№ 1.313(3)	

Clinical Cases & Operating Positions







Fixing Accessories for Saddle Matrices



#1.033

Tines of rings & springclips for installation of saddle matrices are narrowed



#1.033c Ring with Safety Cover



#1.033A

Extra loop on the ring makes it more flexible and allows to operate in wider range of openings without increase of residual distance between the tines



#1.003 Springclip, Small for saddle matrices

#1.005 Springclip, Large for saddle matrices

TOR VM Manufacturing Company Moscow, Russia phone +7(495) 2255417 e-mail: torvm77@gmail.com www.torvm.ru

Clinical Cases & Operating Positions

Representative in USA and Canada TASHMED Winnipeg MB, Canada phone (204) 299-5635, (204) 619-4372 e-mail: info@tashmed.com www.tashmed.com

EU Representative Mr. Gregor Kostunov Untere Seegasse 54, DE-69124 Heidelberg, Germany tel. +49/17)626400019 e-mail: tor.vm.de@googlemail.com www.greko-dental.de



The greatest selection of matrix systems Rubber dam clamps Polishing & Finishing

Anterior Strips & Matrices

- Anatomically pre-shaped
- Five shapes Stainless steel
- Can be used upon restoration of proximal surfaces of anteriors

Available Packages:



1.888 New Anterior Strips & Matrices 30 pcs.

Refills:

#1.387A / #1.387 / #1.388 Proximal anterior strips 12 pcs.

#1.523 / #1.533 New Twin anterior matrices

Operating Positions





Contact & Shape Formers

Stainless steel

Can be used for modelling of: contact point, slope of posterior dental cusp, anterior vestibular surface

Available Packages:



Contact & Shape Former contact former #1.943 - 1 pc. handle #1.100 - 1 pc., shape-former caps #1.863, 1.867, 1.868 - per 10 pcs.

#1.943 / #1.1901 / #1.1902 / #1.1904 Contact former 1 pc.

#1.863 / #1.867 / #1.868 Operating Positions

Add-On Wedges & Tubes, Shape-Former Caps

- Special silicone rubber
- Two types of add-on wedges
- Two types of add-on tubes
- Three types of shape-former caps

Available Packages: Add-on fixing wedges & tubes



#1.870 **New**Add-on fixing wedges of 2 types with Delta ring #1.299, 40 pcs. Refills:

#1.861 / #1.866 Add-on wedges, 40 pcs.

#1.862 Add-on tubes, 40 pcs.

Shape-former caps New Refills for #1.965:



#1.863 10 pcs. #1.867 10 pcs

#1.868 10 pcs Operating Position & Installation Mode





Metal Contoured Matrices

- Anatomically pre-shaped
- Six types of premolar matrices and seven types of molar matrices
- Provide perfect approximal form and contact
- Stainless steel, 0.05 & 0.035 mm thick



Operating Positions





Available Packages:

Premolar / molar matrices universal kit

matrices of 5 types 30 pcs.

Premolar / molar matrices

#1.500+ / #1.510+

#1.501-1.506 /

Refills

Matrices Combined with Clamp

- Anatomically pre-shaped
- Ideal approximal contact
- Tight fitting within a few seconds
- Five types of premolar matrices and five types of molar matrices
- Stainless steel, 0.035 mm thick



No matrix retainer required



#1.540 / #1.550 Premolar / molar matrices universal kit matrices of 5 types 16 pcs.

Available Packages:

#1.560 Premolar & molar matrices 10 pcs.

Refills #1.541-1.545 / #1.551-1.555 Premolar / molar matrices 10 pcs.

Operating Positions





Pony Matrices & Slot Retainers

- Anatomically pre-shaped

- Four types
 Provide perfect approximal form and contact
 Have intermediate length between contoured matrices and sectional matrices Stainless steel, 0.05 & 0.035 mm
- Ring and springclip with special slots for matrix edges





#1.340 / #1.350 Matrices of 4 types with Slot springclip / Slot ring 24 pcs.

Refills: #1.341-1.344 12 pcs.

#1.004 / #1.044 / #1.044c Slot springclip / Slot ring / Slot ring with Silicone Safety Cover

Operating Positions





Metal Matrix Bands

- Four types for premolars and five types for molars
- Stainless steel, 0.05 & 0.035 mm thick

Available Packages:





Plastic-Metal Combined Matrix Bands

#1.0930, 1.0932, 1.0933,1.0935/ #1.0931-1.1933, 1.1935, 1.1937 Premolar / molar matrix bands 12 pcs.

#1.380 / #1.381 Matrix bands 6 / 7 mm wide 12 pcs. (available only 0.035 mm thick)

- Half-plastic / half metal Metal part simplifies matrix penetration through a tight contact point

Available Packages:

#1.034 / #1.134 Premolar / molar matrix bands 12 pcs.



Metal Striprolls

- Stainless steel. 0,05 & 0,035 mm thick
- Two types of package round box & squared box

Available Packages:



#1.390/#1.391 Striproll 3 m in length, 6/7mm wide #1.392/#1.393 Striproll 3 m in length, 6/7mm wide

Striprolls of alternative lengths and widths can be supplied upon special request

Metal Strips

Metal strips are recommended to be used as protective plates of adjacent teeth from accidental bur contact.

Available Packages:



#1.382 / #1.383 Metal strips 6 mm wide, 50 mm in length, 0.06 / 0.09 mm thick 100 pcs.

Perforated Prophylactic Metal Strips

Available Packages:

1.386 Metal Strips for Tartar Removal 4 mm wide, 100 mm in length, 0.05 mm thick 12 pcs.



Perforated Metal Matrices

- Flat & contoured
- Five types
- Stainless steel, 0.05 mm thick

Available Packages:



Ring with Silicone Safety Cover

Springclip #1.002

Operating Positions





ontoured matrices. 12 pcs

#1.331(1)-1.331(5) Flat matrices. 12 pcs.

#1 531(1)-1 531(5)

EU Representative Mr. Gregor Kostunov Untere Seegasse 54, DE-69124 Heidelberg, Germany tel. +49(17)626400019 e-mail: tor.vm.de@googlemail.com www.greko-dental.de

TOR VM Manufacturing Company Moscow, Russia phone +7(495) 2255417 e-mail: torvm77@gmail.com www.torvm.ru

Representative in USA and Canada TASHMED Winnipeg MB, Canada phone (204) 299-5635, (204) 619-4372 e-mail: info@tashmed.com www.tashmed.com

The greatest selection of matrix systems Rubber dam clamps Polishing & Finishing

Fixing Wooden Wedges

- Seven types of anatomically shaped wooden wedges
- One type of trigonal wooden wedges



- Maple wood







Available Packages:

Refills: #1.181-1.187 100 pcs.

Trigonal wedges (medium)
100 pcs.

#1.281

#1.085 / #1.083 / #1.080 Wedges of 6 / 4 / 2 types 400 / 200 / 100 pcs.

Fixing Plastic Wedges

- Anatomically shaped
- Soft plastic
- Transparent & non-transparent
- Two types: thin & medium





Operating Positions





Available Packages:

#1.820 / #1.810 Transparent wedges. 2 types. 80 / 40 pcs.

Refills: #1.811 / #1.812 Thin/Medium transparent wedges. 40 pcs.


#1.840 Non-transparent wedges. 2 types. 80 pcs.

#1.841 / #1.842 Thin/Medium non-transparent wedges.



Elastic Wedges

- Special silicone rubber
- Two thicknesses: 2,5 mm (blue) & 2,0 mm (yellow)





Operating Positions

Available Packages:

#1.808 Blue & yellow wedges, 40 pcs.

Refills: #1.801 / #1.802 Blue / yellow wedges, 10 pcs.



Transparent Contoured Matrices

- Anatomically pre-shaped
- Four types of premolar matrices and four types of molar matrices
- Provide perfect approximal form





#1.092 Premolar & molar matrices, 4 + 4 types, 120 pcs.

#1.190 / #1.191 Premolar / molar matrices of 4 types, 60 pcs.

#1.090(1)-(4) / #1.091(1)-(4) Premolar / molar matrice

Clinical Cases & Operating Positions





Transparent Self-Adhesive Matrices

Four types for molars and four types for premolars

Matrix ends are covered with a special glue layer for side-to-side conjunction

Available Packages:







#1 490 Matrices for premolars 12 pcs.

#1.491 Matrices for molars 12 pcs.

Clinical Cases & Operating Positions






Matrices Combined with Clamp

- Transparent functional surface - Three - dimensional
- shape
- The ideal approximal contact
 Tight fitting within a few seconds
- Four types of premolar & five
- types of molar matrices







Available Packages:

#1.096

#1.094(1)-(4) / #1.095(1)-(4) Premolar / molar matrices 10 pcs.

Clinical Cases & Operating Positions





Transparent Sectional Matrices

- Anatomically pre-shaped
- Provide tight anatomical contact
- Two widths of operating part: 5 & 7 mm - Installed with transparent wedges
- or ring for sectional matrices



Available Packages:



#1.922 Narrow matrices, 30 pcs.

Wide matrices, 30 pcs.

Clinical Cases & Operating Positions





Transparent Crowns. Crown Kits

- 16 individual shapes for incisors & cannines
- 16 individual shapes for
- premolars & molars 8 individual shapes of deciduous
- crowns for incisors & canines 8 individual shapes of deciduous
- crowns for premolars & molars
- 8 types of conical crowns

Available Packages:

Operating Position



#1.910 Anterior Crowns of 16 types, 64 pcs. #1.911 Posterior Crowns of 16 types, 64 pcs.

#1.912 Deciduous Crowns of 16 types, 64 pcs.

#1.901/#1.903/#1.905/ #1.907/#1.908/#1.909 Crowns on plates 12/16/17/18/12/12 pcs. per plate

#1.915 Conical Crowns of 8 types, 64 pcs.



Transparent Strips & Striprolls

- 0.05 mm thick - 8 & 10 mm wide

Available Packages:

#1.040 / #1.041 Strips 8 / 10 mm wide. 100 pcs. #1 440 / #1 441

Stopstrips 8 / 10 mm wide. 12 pcs.





#1.242 / #1.243 Striprolls 8 / 10 mm wide (squared box)

#1.244 / #1.245 Striprolls 8 / 10 mm wide (squared box with cutter)

Transparent Cervical Matrix System

simple and effective tool for class V restorations





#1.141
Transparent Cervical Matrix Bands
Matrix bands, 100 pcs.
Cervical former 1 pc.
Stopper 1 pc.



Representative in USA and Canada TASHMED Winnipeg MB, Canada phone (204) 299-5635, (204) 619-4372 e-mail: info@tashmed.com www.tashmed.com

EU Representative Mr. Gregor Kostunov Untere Seegasse 54, DE-69124 Heidelberg, Germany tel. +49/17)626400019 e-mail: tor.vm.de@googlemail.com www.greko-dental.de

The greatest selection of matrix systems Rubber dam clamps **Polishing & Finishing**

Rubber Dam Clamps

- High-quality stainless steel
- Perfect shape memory and elastic properties

Brinker Clamps (tissue retractors)





№ W2



№ W2A

Nº 202

Anterior Clamps



Premolar Clamps Symmetrical Design




Nº 2









∕ № 22 Molar Clamps Symmetrical Design













Deciduous Clamps Left-Right Design







Black Clamps

All clamps can be supplied in standard and black modification. Clamps of black modification (black clamps) provide anti-reflection effect for more convenient work.



Rubber Dam Accessories

Rubber Dam Forceps

-High quality stainless steel

Convenient in work





Rubber Dam Organizer

Stainless steel Can be also used for storage and sterilization



#3.909 / #3.912 Stand for 9 / 12 clamps 1 pc.

Rubber Dam Frames



#3.401A / #3.401B / #3.402B / #3.403B Frame 97x72mm/ 93x91mm/103x97mm/128x125mm

Polishing Discs

- Four types

- for gross reduction (blue)
 for contouring (green)
 for finishing (yellow)
 for polishing (white)

Six diameters: 9.5, 10, 12, 12.7, 14 & 16 mm



Discs are effective for finishing and polishing composite restorations including fillings located at proximal area

Available Packages: #1.075 Universal Kit

Discs of 4 types, diameters 12 & 14 mm 80 pcs. + mandrel



#1.069 / #1.070 / #1.071 / #1.072 Discs of 4 types diameter 10 / 12 / 14 / 16 mm 40 pcs. + mandrel

Refills: #1.731-1.734 Discs 40 pcs.

#1.731A, 1.731B, 1.732A, 1.732B Discs 50 pcs.

#1.121 Mandrel 1 pc.

Retractors

- High-quality stainless steel Provide reliable isolation of operating field



#1.019 Tongue and Cheek Retractor (with screw thread for connection with standard mirror handle) 1 pc.

#1.119 Tongue and Cheek Retractor (#1.019 with handle) 1 pc.

#1.013 Lip and Cheek Retractor

Cotton Roll Holder

- High-quality stainless steel
- Provide reliable fixation of cotton rolls during dental procedures



#1.010 Cotton Roll Holder





New

Stem Polishing Discs

- Four types:
 for gross reduction (blue)
 for contouring (green)
 for finishing (yellow)
 for polishing (white)

Three diameters: 8,12 &14 mm









The functional surface is free of connection elements. Easy to polish hard-to-reach composite fillings.

Available Packages: #1.600 Universal Kit Discs of 4 types, 3 diameters, including discs with back abrasive position 80 pcs + mandrel

#1.610 / #1.620 / #1.630 Discs of 4 types diameter 8 / 12 / 14 mm 40 pcs + mandrel Refills: #1.611-1.614 / #1.621-1.624 / #1.631-1.634

scs, diameter 8 / 12 / 14 mm Discs, 40 pcs.

#1.111 Mandrel 1 pc.

Loop Matrices

- 2 height of matrix band:
- simplicity of loop length regulation in accordance to loop size
- installed without retained

Available Packages:





#1.597 Loop matrices height 7 mm,

Mainly to be used for protection of adjacent tooth against bur upon cavity preparation.

Operating Positions





Polishing & Finishing Strips

Three types:

- for gross reduction (blue) / for contouring (green)
- for contouring (green) for finishing (yellow)
- for finishing (yellow) / for polishing (white)







#1.051 Strips for contouring 25 pcs.

Available Packages:



#1.055 Strips for gross reduction, contouring & polishing 75 pcs.

EU Representative Mr. Gregor Kostunov Untere Seegasse 54, DE-69124 Heidelberg, Germany tel. +49(17)626400019 e-mail: tor.vm.de@googlemail.com www.greko-dental.de

TOR VM Manufacturing Company Moscow, Russia phone +7(495) 2255417 e-mail: torvm77@gmail.com www.torvm.ru

Representative in USA and Canada TASHMED Winnipeg MB, Canada phone (204) 299-5635, (204) 619-4372 e-mail: info@tashmed.com www.tashmed.com